

CUT YELLOW, BLUE AND WHITE WIRES GOING FROM CONTROL BOX TO BACK-CHECK SWITCH ON OPERATOR CAM.
 YELLOW AND BLUE FROM CAM SWITCH USED FOR COIL ACTIVATION SEE FIGURE 2. TERM 7 & 8
 YELLOW TERM(5) BLUE TERM (1) WHITE TERM (3) FROM CONTROL BOX TO ISO RELAY CONTACTS. FIGURE 1
 TO TERM 6 & 2 SERIES INTO NORMALLY OPEN CIRCUITS FOR SAFETY SLOW, CONTROL BOX SAFETY TO (SWING). FIGURE 3.





FIGURE 1: WIRING FROM CONTROL BOX FOR BACK CHECK




FIGURE 2



B.E.A., Inc.
 100 Enterprise Drive, Pittsburgh, PA 15275
 PH: (412) 249-4100 FAX: (412) 249-4101

**TITLE: GYROTECH 300/400/500
 STAND ALONE SUPERSCANS**

| SIZE | CAGE CODE | DMGNO | FILE OF: | DRAWN BY: | REV |
|-------|-----------|---------|-----------|-----------|--------|
| A | | 80.0089 | ENG'G | JED | 01 |
| SCALE | NONE | DATE: | 05 JAN 04 | SHEET | 1 OF 1 |